

TECHNICAL DATA SHEET

Part No. 111-01715
Article No. 111-01715
Type WSS



The Heavy Duty Wide-Strap Cable Tie was designed to minimize the pinching of soft bundles and the potential of lateral movement along the bundle. The low-profile head and underside clamping rails increase the grip around the bundle and provide a better fit than traditional cable ties. These are used primarily in the trucking and heavy equipment industries, but can be used in a wide variety of applications where strength is needed.

Material	Polyamide 4.6 (PA46)
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Brown (BN)
Pkg. Qty.	300
Carton Qty.	1200
Customs Number	3926909988

Length (imperial)	9.06 "
Length (metric)	230.0 mm
Max. Bundle Diameter (imperial)	2.25 "
Max. Bundle Diameter (metric)	57.1 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Serration Side	Inside Serrated
Thickness (imperial)	0.055 "
Thickness (metric)	1.4 mm
Width (imperial)	0.50 "
Width (metric)	12.7 mm

