

TECHNICAL DATA SHEET

Part No. T30R9HSM4
Article No. 111-03069
Type T30R



HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	5000
Customs Number	3926909988

Length (imperial)	5.83 "
Length (metric)	148.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	30 lbs
Min. Tensile Strength (metric)	135 N
Serration Side	Inside Serrated
Thickness (metric)	1.1 mm
Width (imperial)	0.14 "
Width (metric)	3.6 mm

