

TECHNICAL DATA SHEET

Part No. 111-02495
Article No. 111-02495
Type T150M



Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 V0 (PA66V0)
Operating Temperature	-40°F to +212°F (-40°C to +100°C)
Flammability	UL 94 V-0
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	1000
Customs Number	3926909988

Length (imperial)	21.0 "
Length (metric)	530.0 mm
Max. Bundle Diameter (imperial)	5.91 "
Max. Bundle Diameter (metric)	150.0 mm
Min. Tensile Strength (imperial)	175 lbs
Min. Tensile Strength (metric)	780 N
Serration Side	Inside Serrated
Thickness (metric)	1.9 mm
Width (imperial)	0.35 "
Width (metric)	8.9 mm

