

TECHNICAL DATA SHEET

Part No. 111-02496
Article No. 111-02496
Type WSI



The Heavy Duty Wide-Strap Cable Tie was designed to minimize the pinching of soft bundles and the potential of lateral movement along the bundle. The low-profile head and underside clamping rails increase the grip around the bundle and provide a better fit than traditional cable ties. Can be used in a wide variety of applications where strength is needed.

Material	Polyamide 6.6 V0 (PA66V0)
Operating Temperature	-40°F to +212°F (-40°C to +100°C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	300
Carton Qty.	1200
Customs Number	3926909988

Cable Tie Head Width (metric)	19.81 mm
Length (imperial)	12.1 "
Length (metric)	307.0 mm
Max. Bundle Diameter (imperial)	3.25 "
Max. Bundle Diameter (metric)	82.5 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Serration Side	Inside Serrated
Width (imperial)	0.50 "
Width (metric)	12.7 mm

