

TECHNICAL DATA SHEET

Part No. 111-08280
Article No. 111-08280
Type T80I



HellermannTyton manufactures a full line of high quality cable ties in a variety of styles, sizes, materials, and colors. HellermannTyton cable ties are engineered and manufactured for maximum performance and quality.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	7000
Customs Number	3926909988

Length (imperial)	12.0 "
Length (metric)	305.0 mm
Max. Bundle Diameter (imperial)	3.35 "
Max. Bundle Diameter (metric)	85.0 mm
Min. Tensile Strength (imperial)	80 lbs
Min. Tensile Strength (metric)	355 N
Serration Side	Inside Serrated
Thickness (metric)	1.3 mm
Width (imperial)	0.19 "
Width (metric)	4.7 mm

