

TECHNICAL DATA SHEET

Part No. T150XL0X2
Article No. 111-15500
Type T150XL



Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	500
Customs Number	3926909988

Length (imperial)	43.0 "
Length (metric)	1095.0 mm
Max. Bundle Diameter (imperial)	12.99 "
Max. Bundle Diameter (metric)	330.0 mm
Min. Tensile Strength (imperial)	175 lbs
Min. Tensile Strength (metric)	780 N
Serration Side	Inside Serrated
Thickness (imperial)	0.083 "
Thickness (metric)	2.1 mm
Width (imperial)	0.35 "
Width (metric)	8.9 mm

