

TECHNICAL DATA SHEET

Part No. T255M0HIRX2
Article No. 111-25300
Type T255M



HellermannTyton's T255 series heavy duty cable ties are ideal for bundles demanding a strong cable tie that may also require a higher temperature rating than the T250 series. These ties have a tensile strength of 250 lbs. Heavy-Duty T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	500
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.61 "
Cable Tie Head Length (metric)	15.5 mm
Cable Tie Head Width (imperial)	0.80 "
Cable Tie Head Width (metric)	20.0 mm
Length (imperial)	22.0 "
Length (metric)	560.0 mm
Max. Bundle Diameter (imperial)	6.3 "
Max. Bundle Diameter (metric)	160.0 mm
Min. Tensile Strength (imperial)	255 lbs
Min. Tensile Strength (metric)	1134 N
Serration Side	Inside Serrated
Width (imperial)	0.50 "
Width (metric)	12.7 mm

