

TECHNICAL DATA SHEET

Part No. T150LL9X2
Article No. 111-15719
Type T150LL



HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	25
Carton Qty.	500
Customs Number	3926909988

Length (imperial)	36.4 "
Length (metric)	925.0 mm
Max. Bundle Diameter (imperial)	10.8 "
Max. Bundle Diameter (metric)	274.3 mm
Min. Tensile Strength (imperial)	175 lbs
Min. Tensile Strength (metric)	780 N
Serration Side	Inside Serrated
Thickness (imperial)	0.079 "
Thickness (metric)	2 mm
Width (imperial)	0.35 "
Width (metric)	8.9 mm

