

TECHNICAL DATA SHEET

Part No. T255R0HIRX2
Article No. 111-25400
Type T255R



HellermannTyton's T255 series heavy duty cable ties are ideal for bundles demanding a strong cable tie that may also require a higher impact resistance than the T250 series. These ties have a tensile strength of 250 pounds. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	500
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.61 "
Cable Tie Head Length (metric)	15.5 mm
Cable Tie Head Width (imperial)	0.80 "
Cable Tie Head Width (metric)	20.0 mm
Height (imperial)	0.37 "
Height (metric)	9.3 mm
Length (imperial)	20.0 "
Length (metric)	508.0 mm
Max. Bundle Diameter (imperial)	5.0 "
Max. Bundle Diameter (metric)	127.0 mm
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Serration Side	Inside Serrated
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.50 "
Width (metric)	12.7 mm

