

TECHNICAL DATA SHEET

Part No. TELS-H
Article No. 111-31000
Type EL-TY (TELSH)



Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with stainless steel pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.

Material	Polyacetal, UV stabilized (POMUV) with stainless steel pawl (SS)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	3000
Customs Number	3926909988

Content of Set/Kit	25 Heads
Height (imperial)	0.49 "
Height (metric)	12.40 mm
Length (imperial)	0.62 "
Length (metric)	15.75 mm
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Serration Side	Not Serrated
Width (imperial)	0.8 "
Width (metric)	20.3 mm
Width 2 (imperial)	0.8 "
Width 2 (metric)	20.3 mm

RoHS ✓