

TECHNICAL DATA SHEET

Part No. TELS-24STRAP
Article No. 111-32109
Type TELS-24STRAP



Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with stainless steel pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.

Material	Polyacetal (POM)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	500
Customs Number	3926909988

Length (imperial)	24.0 "
Length (metric)	610.0 mm
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Serration Side	Not Serrated
Width (imperial)	0.5 "
Width (metric)	12.7 mm

RoHS✓