

TECHNICAL DATA SHEET

Part No. 115-00030
Article No. 115-00030
Type SpeedyTie (RTT750HR)



HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes or temporary bundling are necessary. The head design guarantees high tensile strength even after repeated use.

Material	Polyamide 6.6, high impact modified, scan black (PA66HIR(S))
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5
Carton Qty.	60
Customs Number	3926909988

Length (imperial)	29.6 "
Length (metric)	752.0 mm
Max. Bundle Diameter (metric)	210.0 mm
Min. Tensile Strength (imperial)	200 lbs
Min. Tensile Strength (metric)	888 N
Thickness (imperial)	0.075 "
Thickness (metric)	1.9 mm
Width (imperial)	0.51 "
Width (metric)	13.0 mm

RoHS 