

TECHNICAL DATA SHEET

Part No. 111-32119
Article No. 111-32119
Type TELS-REEL



Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with copper alloy pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.

Material	Polyacetal (POM)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	1
Carton Qty.	1 Reel
Customs Number	3926909988

Length (imperial)	1000.0 ft
Length (metric)	304.8 m
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Serration Side	Not Serrated
Thickness (imperial)	0.06 "
Thickness (metric)	1.50 mm
Width (imperial)	0.5 "
Width (metric)	12.8 mm

