

TECHNICAL DATA SHEET

Part No. 111-85720
Article No. 111-85720
Type T50RSFM



Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	8000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.22 "
Length (imperial)	8.0 "
Length (metric)	205 mm
Max. Bundle Diameter (imperial)	1.77 "
Max. Bundle Diameter (metric)	45.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.26 "
Mounting Hole Diameter (metric)	6.0 - 6.6 mm
Panel Thickness (imperial)	0.03 - 0.12 "
Panel Thickness (metric)	0.7 - 3.0 mm
Thickness (metric)	1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

