

TECHNICAL DATA SHEET

Part No. RT250S0X2
Article No. 115-41800
Type RT250S



HellermannTyton heavy-duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	1000
Customs Number	3926909988

Length (imperial)	9.1 "
Length (metric)	230.0 mm
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Width (imperial)	0.49 "
Width (metric)	12.5 mm

