

# TECHNICAL DATA SHEET

**Part No.** T30R0UVC2  
**Article No.** 112-03060  
**Type** T30R



Used in the solar industry and other applications, HellermannTyton offers cable ties made of UV stabilized PA66UV material. This material provides additional protection against UV radiation for long-term outdoor use and is available in various styles, tensile strengths, and bundle diameters. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

<b>Material</b>	Polyamide 6.6 UV-resistant (PA66UV)
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>Flammability</b>	UL 94 V-2
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	100
<b>Carton Qty.</b>	5000
<b>Customs Number</b>	3926909988

<b>Length (imperial)</b>	5.83 "
<b>Length (metric)</b>	148.0 mm
<b>Max. Bundle Diameter (imperial)</b>	1.38 "
<b>Max. Bundle Diameter (metric)</b>	35.0 mm
<b>Min. Tensile Strength (imperial)</b>	30 lbs
<b>Min. Tensile Strength (metric)</b>	135 N
<b>Serration Side</b>	Inside Serrated
<b>Thickness (imperial)</b>	0.05 "
<b>Thickness (metric)</b>	1.2 mm
<b>Width (imperial)</b>	0.14 "
<b>Width (metric)</b>	3.6 mm

