

TECHNICAL DATA SHEET

Part No. 151-02104
Article No. 151-02104
Type HDM375BDM4W-R



High Torque Double Mounts are designed for use with power assisted impact wrenches and are molded with a metal bushing to withstand the forces required to tighten grade 8 bolts. Mounts are designed for routing multiple bundles with HellermannTyton heavy duty T250, T255, and wide strap cable ties to harness wires and hoses. The bundle is secured directly over the mounting fastener. The arched saddle surface allows for a broad surface contact with the bundle, minimizing pinching and crushing of the bundles. Mounts accept all standard cable ties up to .5" wide.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	100
Carton Qty.	100
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
Height (imperial)	0.99 "
Height (metric)	25.2 mm
Length (imperial)	3.50 "
Length (metric)	89.0 mm
Max. Cable Tie Width (imperial)	0.5 "
Max. Cable Tie Width (metric)	12.7 mm
Mounting Screw Type	3/8" (M10) Screw
Width (imperial)	1.4 "
Width (metric)	34.1 mm

