

# TECHNICAL DATA SHEET

**Part No.** 151-02219  
**Article No.** 151-02219  
**Type** FMB4APT-A



HellermannTyton FlexTack Adhesive Cable Tie Mounts deliver excellent mounting performance on flat, curved and moderately angled surfaces. Use in combination with 18- through 50-pound cable ties to provide stability when securing bundles. The adhesive on this mount is approved for use on low- to medium-energy surfaces in automotive applications, such as clear-coats and plastics; railway, aerospace and heavy equipment; and where drilling a hole is not possible or desirable. The 4-way saddle allows cable ties to be inserted parallel or perpendicular to the wire bundles.

|                              |                                        |
|------------------------------|----------------------------------------|
| <b>Material</b>              | Polyamide 6.6 heat stabilized (PA66HS) |
| <b>Adhesive</b>              | Acrylate with base of acrylic foam     |
| <b>Operating Temperature</b> | -40°F to +194°F (-40°C to +90°C)       |
| <b>Flammability</b>          | UL 94 V-2 (excluding adhesive)         |
| <b>Halogen Free</b>          | Yes                                    |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use             |
| <b>Color</b>                 | Black (BK)                             |
| <b>Pkg. Qty.</b>             | 100                                    |
| <b>Carton Qty.</b>           | 5000                                   |
| <b>Customs Number</b>        | 3926909988                             |

|                                    |            |
|------------------------------------|------------|
| <b>Fixation Method</b>             | Adhesive   |
| <b>For Cable Tie Series</b>        | T18 - T50  |
| <b>Height (imperial)</b>           | 0.25 "     |
| <b>Height (metric)</b>             | 6.3 mm     |
| <b>Length (imperial)</b>           | 1.1 "      |
| <b>Length (metric)</b>             | 28.0 mm    |
| <b>Max. Static Load (imperial)</b> | 1.1 lbf-ft |
| <b>Maximum Static Load (N)</b>     | 1.49 N     |
| <b>Width (imperial)</b>            | 1.1 "      |
| <b>Width (metric)</b>              | 28.0 mm    |

