

TECHNICAL DATA SHEET

Part No. 151-02877
Article No. 151-02877
Type RCD90SM8



The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws.

Material	Polyamide 6.6/6, V0 (PA666V0), Steel (ST), Zinc plated (ZN)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	160
Carton Qty.	160
Customs Number	3926909988

Angle	90 °
Length (imperial)	6.58 "
Length (metric)	167.2 mm
Length 2 (imperial)	3.99 "
Length 2 (metric)	101.2 mm
Max. Bundle Diameter (imperial)	2.01 "
Max. Bundle Diameter (metric)	51.0 mm
Min. Bundle Diameter (imperial)	1.42 "
Min. Bundle Diameter (metric)	36.0 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Mounting Hole Centers (imperial)	2.62 "
Mounting Hole Centers (metric)	66.5 mm
Mounting Hole Diameter (imperial)	0.33 "
Mounting Hole Diameter (metric)	8.4 mm
Width (imperial)	1.37 "
Width (metric)	34.9 mm

HF ✓

LFH ✓

RoHS ✓

EN 45545-2

ASTM