

# TECHNICAL DATA SHEET

**Part No.** 117-00015  
**Article No.** 117-00015  
**Type** T120RDH



The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

|                              |                                        |
|------------------------------|----------------------------------------|
| <b>Material</b>              | Polyamide 6.6 heat stabilized (PA66HS) |
| <b>Operating Temperature</b> | -40°F to +257°F (-40°C to +125°C)      |
| <b>Flammability</b>          | UL 94 V-2                              |
| <b>UV Resistant</b>          | Yes                                    |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use             |
| <b>Color</b>                 | Black (BK)                             |
| <b>Pkg. Qty.</b>             | 500                                    |
| <b>Carton Qty.</b>           | 1000                                   |
| <b>Customs Number</b>        | 3926909988                             |

|                                         |                 |
|-----------------------------------------|-----------------|
| <b>Cable Tie Head Length (imperial)</b> | 0.9 "           |
| <b>Cable Tie Head Length (metric)</b>   | 22.9 mm         |
| <b>Cable Tie Head Width (imperial)</b>  | 0.48 "          |
| <b>Cable Tie Head Width (metric)</b>    | 12.3 mm         |
| <b>Length (imperial)</b>                | 15.7 "          |
| <b>Length (metric)</b>                  | 398.0 mm        |
| <b>Max. Bundle Diameter (imperial)</b>  | 4.0 "           |
| <b>Max. Bundle Diameter (metric)</b>    | 101.6 mm        |
| <b>Min. Tensile Strength (imperial)</b> | 120 lbs         |
| <b>Min. Tensile Strength (metric)</b>   | 534 N           |
| <b>Serration Side</b>                   | Inside Serrated |
| <b>Thickness (imperial)</b>             | 0.07 "          |
| <b>Thickness (metric)</b>               | 1.8 mm          |
| <b>Width (imperial)</b>                 | 0.30 "          |
| <b>Width (metric)</b>                   | 7.6 mm          |

