

TECHNICAL DATA SHEET

Part No. 156-00155
Article No. 156-00155
Type T50SVC6.5



HellermannTyton's simple to use self-affixing tie allows the attaching of wires or hoses to an existing harness. This allows 360 degree rotation, and the ability to be oriented in any direction in relation to the main harness. This is ideally suited for any application in which the wire or hose can move in relation to the fixing point.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	6000
Customs Number	3926909988

Attaches to Diameter (imperial)	0.26 - 0.31 "
Attaches to Diameter (metric)	6.5 - 8.0 mm
Length (imperial)	6.1 "
Length (metric)	155.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	222 N
Width (imperial)	0.19 "
Width (metric)	4.7 mm

RoHS✓