

TECHNICAL DATA SHEET

Part No. 156-00594
Article No. 156-00594
Type T50ROC2



HellermannTyton's 2-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.

Material	Polyamide 6.6 heat and UV stabilized (PA66HSUV), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Cable Tie	PA66UV
Material Foot Part	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	4000
Customs Number	3926909988

Attaches to Diameter (imperial)	0.26 - 0.30 "
Attaches to Diameter (metric)	6.5 - 7.5 mm
Length (imperial)	8.0 "
Length (metric)	202.0 mm
Max. Bundle Diameter (imperial)	1.77 "
Max. Bundle Diameter (metric)	45.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS