

TECHNICAL DATA SHEET

Part No. 117-00028
Article No. 117-00028
Type T120RDH



The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Orange (OG), High Voltage (HV)
Pkg. Qty.	1000
Carton Qty.	1000 Pieces
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.9 "
Cable Tie Head Length (metric)	22.9 mm
Cable Tie Head Width (imperial)	0.48 "
Cable Tie Head Width (metric)	12.3 mm
Height (imperial)	0.29 "
Height (metric)	7.5 mm
Length (imperial)	15.7 "
Length (metric)	398.0 mm
Max. Bundle Diameter (imperial)	4.0 "
Max. Bundle Diameter (metric)	101.6 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	534 N
Serration Side	Inside Serrated
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

HF ✓

RoHS ✓