

TECHNICAL DATA SHEET

Part No. 156-01429
Article No. 156-01429
Type T50RSB8SET



Unique, two-piece design allows routing to be above, parallel or perpendicular to stud. This also enables up to three separate bundles to be fastened to the same stud. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.29 "
Cable Tie Head Length (metric)	7.3 mm
Cable Tie Head Width (imperial)	0.3 "
Cable Tie Head Width (metric)	7.6 mm
Fixation Method	Stud Mount
Height (imperial)	0.98 "
Height (metric)	25.0 mm
Length (imperial)	7.95 "
Length (metric)	202.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Stud Diameter (imperial)	0.31 "
Stud Diameter (metric)	8.0 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.181 "
Width (metric)	4.6 mm

