

# TECHNICAL DATA SHEET

**Part No.** 156-01661  
**Article No.** 156-01661  
**Type** T50RMOC9SAD-SET



The MOC with Saddle to T50R Tie has a two-piece design that keeps two routings secured together while providing a fixed orientation for each bundle. The bi-directional saddle design allows the bundles to be coupled parallel or perpendicular to one another. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness.

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                        |
| <b>Flammability</b>          | UL 94 HB                                                                 |
| <b>Halogen Free</b>          | Yes                                                                      |
| <b>UV Resistant</b>          | Yes                                                                      |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                               |
| <b>Color</b>                 | Black (BK)                                                               |
| <b>Pkg. Qty.</b>             | 5000                                                                     |
| <b>Carton Qty.</b>           | 5000                                                                     |
| <b>Customs Number</b>        | 3926909988                                                               |

|                                           |         |
|-------------------------------------------|---------|
| <b>Height (imperial)</b>                  | 0.92 "  |
| <b>Height (metric)</b>                    | 23.4 mm |
| <b>Length (imperial)</b>                  | 0.59 "  |
| <b>Length (metric)</b>                    | 15.0 mm |
| <b>Max. Bundle Diameter (imperial)</b>    | 0.39 "  |
| <b>Max. Bundle Diameter (metric)</b>      | 10.0 mm |
| <b>Min. Bundle Diameter (imperial)</b>    | 0.31 "  |
| <b>Min. Bundle Diameter (metric)</b>      | 8.0 mm  |
| <b>Min. Tensile Strength (imperial)</b>   | 50 lbs  |
| <b>Min. Tensile Strength (metric)</b>     | 225 N   |
| <b>Nominal Bundle Diameter (imperial)</b> | 0.35"   |
| <b>Nominal Bundle Diameter (metric)</b>   | 9.0 mm  |

