

# TECHNICAL DATA SHEET

**Part No.** 156-01787  
**Article No.** 156-01787  
**Type** T50SMVCMOC10M180



The MOC 180 to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The clip's orientation allows the second routing to be assembled in the direction of the first routing. The swivel coupler allows the two routings to rotate independently of each other.

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                        |
| <b>Flammability</b>          | UL 94 HB                                                                 |
| <b>Halogen Free</b>          | Yes                                                                      |
| <b>UV Resistant</b>          | Yes                                                                      |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                               |
| <b>Color</b>                 | Black (BK)                                                               |
| <b>Pkg. Qty.</b>             | 1000                                                                     |
| <b>Carton Qty.</b>           | 1000                                                                     |
| <b>Customs Number</b>        | 3926909988                                                               |

|                                           |         |
|-------------------------------------------|---------|
| <b>Height (imperial)</b>                  | 1.35 "  |
| <b>Height (metric)</b>                    | 34.2 mm |
| <b>Length (imperial)</b>                  | 0.67 "  |
| <b>Length (metric)</b>                    | 16.9 mm |
| <b>Length 2 (imperial)</b>                | 0.64 "  |
| <b>Length 2 (metric)</b>                  | 16.3 mm |
| <b>Max. Bundle Diameter (imperial)</b>    | 0.45 "  |
| <b>Max. Bundle Diameter (metric)</b>      | 11.5 mm |
| <b>Min. Bundle Diameter (imperial)</b>    | 0.37 "  |
| <b>Min. Bundle Diameter (metric)</b>      | 9.5 mm  |
| <b>Min. Tensile Strength (imperial)</b>   | 50 lbs  |
| <b>Min. Tensile Strength (metric)</b>     | 225 N   |
| <b>Nominal Bundle Diameter (imperial)</b> | 0.39"   |
| <b>Nominal Bundle Diameter (metric)</b>   | 10.0 mm |

