

TECHNICAL DATA SHEET

Part No. 126-03100
Article No. 126-03100
Type T50SOSSFT6.5E-MDL



Arrowhead Push Ties with rubber seal secure fast and easy, while providing a special rubber seal to minimize water, dirt, or dust from getting through the mounting hole. The anchor adjusts for variations in panel thicknesses which insures a secure fixing at all times.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Green (GN)
Pkg. Qty.	500
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Arrowhead
Height (imperial)	0.67 "
Length (imperial)	6.3 "
Length (metric)	158.8 mm
Max. Bundle Diameter (imperial)	1.18 "
Max. Bundle Diameter (metric)	30.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 - 0.26 "
Mounting Hole Diameter (metric)	6.3 - 6.7 mm
Panel Thickness (imperial)	0.02 - 0.07 "
Panel Thickness (metric)	0.6 - 1.8 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

RoHS 