

TECHNICAL DATA SHEET

Part No. 151-00997
Article No. 151-00997
Type MCCTAM1



The MCCTAM1 anchor mounts are for use with HellermannTyton MCT18 - MCT50 Series cable ties to provide stability when securing bundles. The Metal Content Mount is specifically designed for the food, beverage and pharmaceutical processing industries to meet the safety standards set by the Hazardous Analysis of Critical Control Point (HACCP). The mount is nylon-based with metal content dispersed throughout allowing for the part to be identified by metal detectors or X-ray inspections, reducing the risk of contamination.

Material	Polyamide 6.6, metal detectable (PA66MD)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Blue (BU)
Pkg. Qty.	100
Carton Qty.	10000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	MCT18 - MCT50
Height (imperial)	0.20 "
Height (metric)	5.1 mm
Length (imperial)	0.81 "
Length (metric)	20.7 mm
Max. Cable Tie Width (imperial)	0.20 "
Max. Cable Tie Width (metric)	5.2 mm
Mounting Hole Diameter (imperial)	0.17 "
Mounting Hole Diameter (metric)	4.3 mm
Mounting Screw Type	M4 Screw
Width (imperial)	0.41 "
Width (metric)	10.3 mm

HF ✓

RoHS ✓