

TECHNICAL DATA SHEET

Part No. 151-03099
Article No. 151-03099
Type MB4



HellermannTyton screw fastened mounting bases are used with 18 through 50 lb cable ties to provide stability when securing bundles. Cable ties can be inserted parallel or perpendicular to the wire bundles. Low fire hazard material is designed specifically for rail applications.

Material	Polyamide 6.6/6, V0 (PA666V0)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T50
Height (imperial)	0.19 "
Height (metric)	4.8 mm
Length (imperial)	1.12 "
Length (metric)	28.5 mm
Max. Cable Tie Width (imperial)	0.18 "
Max. Cable Tie Width (metric)	5.4 mm
Mounting Hole Diameter (imperial)	0.18 "
Mounting Hole Diameter (metric)	4.6 mm
Mounting Screw Type	#8 Screw
Width (imperial)	1.12 "
Width (metric)	28.5 mm

HF ✓

LFH ✓

RoHS ✓

ASTM

NFPA 130