

TECHNICAL DATA SHEET

Part No. 156-01818
Article No. 156-01818
Type T50RMOC16SAD-SET



The MOC with Saddle to T50R Tie has a two-piece design that keeps two routings secured together while providing a fixed orientation for each bundle. The bi-directional saddle design allows the bundles to be coupled parallel or perpendicular to one another. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	1.26 "
Height (metric)	31.9 mm
Length (imperial)	0.90 "
Length (metric)	22.9 mm
Max. Bundle Diameter (imperial)	0.72 "
Max. Bundle Diameter (metric)	18.3 mm
Min. Bundle Diameter (imperial)	0.55 "
Min. Bundle Diameter (metric)	14.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Nominal Bundle Diameter (imperial)	0.63"
Nominal Bundle Diameter (metric)	16.0 mm

