

TECHNICAL DATA SHEET

Part No. 151-04218
Article No. 151-04218
Type CBLSTK3CZS



HellermannTyton's Cable Stacker Mount is a cable management device used to organize and mount wires and relieve congestion along wire pathways found in conveyor systems and automation equipment. These mounts feature individual cradle partitions which enable faster installs and reduced rework and improve appearance and aesthetics. The EZ Build concept holds cables in place via a proprietary compartmental design and retention pins, which separate different types of cabling and, in many cases, eliminate the need for cable ties. Cable Stackers are secured to surfaces using two screws.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	10
Carton Qty.	500 Pieces
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
Height (imperial)	4.21 "
Height (metric)	106.9 mm
Length (imperial)	1.69 "
Length (metric)	43.0 mm
Mounting Hole Diameter (imperial)	0.259 "
Mounting Hole Diameter (metric)	6.6 mm
Mounting Screw Type	#10 Screw, M6 Screw
Width (imperial)	1.42 "
Width (metric)	36.0 mm

HF ✓

RoHS ✓