

TECHNICAL DATA SHEET

Part No. 156-03014
Article No. 156-03014
Type DUALWSRASSY



Couplers simplify connecting two cable ties for routing and separating bundles. Designed to allow up to 90 degrees of rotation, these assemblies are ideal for applications in which the bundle, pipe or hose requires slight movement in relation to the fastening point.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHSUV
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

For Cable Tie Series	T120
Height (imperial)	0.43 "
Height (metric)	10.86 mm
Length (imperial)	15.1 "
Length (metric)	383.0 mm
Max. Bundle Diameter (imperial)	3.86 "
Max. Bundle Diameter (metric)	98.0 mm
Min. Bundle Diameter (imperial)	0.59 "
Min. Bundle Diameter (metric)	15.0 mm
Width (imperial)	0.5 "
Width (metric)	12.7 mm

