

TECHNICAL DATA SHEET

Part No. MB5A0A2F4
Article No. 151-28604
Type MB5A



HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.

Material	Polyamide 6.6 (PA66)
Adhesive	Acrylate with base of polyethylene foam
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Adhesive
For Cable Tie Series	T18 - T150
Height (imperial)	.28 "
Height (metric)	7.1 mm
Length (imperial)	1.49 "
Length (metric)	37.7 mm
Max. Static Load (imperial)	2.1 lbf-ft
Maximum Static Load (N)	9.341 N
Width (imperial)	1.49 "
Width (metric)	37.7 mm

