

TECHNICAL DATA SHEET

Part No. 156-03602
Article No. 156-03602
Type CMRCCHANGERFS7



The Series 7 Ratchet Clamp offers one-handed, toolless simplicity and size versatility for managing wires and cables on First Solar modules. The robust design and solar-optimized materials make it ideal for heavy duty, outdoor applications. One-piece adjustable clamp can be closed by hand to the desired diameter, replacing multiple sizes of single-diameter fasteners. Integrated release feature enables easy and nondestructive removal of cables by inserting a flat-head screwdriver. This allows the clamp to be reused without removing it.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Zinc plated (ZN), Steel (ST)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	150
Carton Qty.	150 Pieces
Customs Number	3926909988

Fixation Method	Mounting Hanger
Length (imperial)	4.93 "
Length (metric)	125.3 mm
Max. Bundle Diameter (imperial)	1.42 "
Max. Bundle Diameter (metric)	36.07 mm
Min. Bundle Diameter (imperial)	0.76 "
Min. Bundle Diameter (metric)	19.3 mm
Min. Tensile Strength (imperial)	100 lbs
Width (imperial)	1.40 "
Width (metric)	35.5 mm

