

# TECHNICAL DATA SHEET

**Part No.** 156-01340  
**Article No.** 156-01340  
**Type** T50SMVCOC15-18



HellermannTyton's 2-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.

|                              |                                                                                                          |
|------------------------------|----------------------------------------------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| <b>Material Cable Tie</b>    | PA66HS                                                                                                   |
| <b>Material Foot Part</b>    | PA66HIRHS                                                                                                |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                                                        |
| <b>Flammability</b>          | UL 94 HB                                                                                                 |
| <b>UV Resistant</b>          | No                                                                                                       |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                                                               |
| <b>Color</b>                 | Black (BK)                                                                                               |
| <b>Pkg. Qty.</b>             | 500                                                                                                      |
| <b>Carton Qty.</b>           | 3000                                                                                                     |
| <b>Customs Number</b>        | 3926909988                                                                                               |

|                                         |                |
|-----------------------------------------|----------------|
| <b>Attaches to Diameter (imperial)</b>  | 0.59 - 0.71 "  |
| <b>Attaches to Diameter (metric)</b>    | 15.0 - 18.0 mm |
| <b>Length (imperial)</b>                | 8.3 "          |
| <b>Length (metric)</b>                  | 210.0 mm       |
| <b>Max. Bundle Diameter (imperial)</b>  | 1.97 "         |
| <b>Max. Bundle Diameter (metric)</b>    | 50.0 mm        |
| <b>Min. Tensile Strength (imperial)</b> | 50 lbs         |
| <b>Min. Tensile Strength (metric)</b>   | 222 N          |
| <b>Width (imperial)</b>                 | 0.19 "         |
| <b>Width (metric)</b>                   | 4.7 mm         |

RoHS