

TECHNICAL DATA SHEET

Part No. 156-04052
Article No. 156-04052
Type T50REC5A



This cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HIRHS
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Orange (OG), High Voltage (HV), Black (BK)
Pkg. Qty.	500
Carton Qty.	4000 Pieces
Customs Number	3926909988

Fixation Method	Edge Clip
Height (imperial)	0.05 "
Height (metric)	1.2 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Length 2 (metric)	14.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Panel Thickness (imperial)	0.04 - 0.12 "
Panel Thickness (metric)	1.0 - 3.0 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

