

TECHNICAL DATA SHEET

Part No. 156-02624
Article No. 156-02624
Type IRCAMB5A



The Adhesive Mount Ratchet Clamp offers versatility when managing wires, cables and hoses. Ultra-strong adhesive base attaches where holes don't exist or are undesirable, so no additional hardware is needed for securing to a or panel. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal of cables simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the mounting surface.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Adhesive	Acrylic
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	250
Customs Number	3926909988

Fixation Method	Adhesive
Length (imperial)	1.37 "
Length (metric)	34.8 mm
Max. Bundle Diameter (imperial)	0.54 "
Max. Bundle Diameter (metric)	13.72 mm
Min. Bundle Diameter (imperial)	0.24 "
Min. Bundle Diameter (metric)	6.10 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Width (imperial)	1.37 "
Width (metric)	34.9 mm

RoHS

