

TECHNICAL DATA SHEET

Part No. 157-00415
Article No. 157-00415
Type T50ROSLPM6SMSO25



One-piece cable tie with stud mount features an offset design to position bundles away from obstructions, heat or sources of abrasion. It includes a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Stud Mount
Height (imperial)	0.05 "
Height (metric)	1.35 mm
Length (imperial)	8.82 "
Length (metric)	224.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Offset Length (imperial)	1.0 "
Offset Length (metric)	25.5 mm
Stud Diameter (imperial)	0.20 ", 0.24 "
Stud Diameter (metric)	5.0 mm, 6.0 mm
Width (imperial)	0.19 "
Width (metric)	14.2 mm

RoHS