

TECHNICAL DATA SHEET

Part No. T120RSM0HIRK2
Article No. 157-01300
Type T120RSM



Stud mount tie designed for use on a 1/4" threaded stud or exposed threads of a machine screw.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	50
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Stud Mount
Height (imperial)	0.77 "
Height (metric)	19.50 mm
Length (imperial)	16.0 "
Length (metric)	405.0 mm
Max. Bundle Diameter (imperial)	3.98 "
Max. Bundle Diameter (metric)	101.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Stud Diameter (imperial)	0.25 "
Stud Diameter (metric)	6.3 mm
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

RoHS