

TECHNICAL DATA SHEET

Part No. 157-04100
Article No. 157-04100
Type T50SOSFT6.5LG-E4



Part of our sustainable line of products, the ReSource product family features solutions made from excess plastic left over from the manufacturing process or from consumers. This fir tree mount is made from 100 percent postindustrial recycled plastic. It provides a secure grip in a mounting hole. The fir tree provides a low push-in force and high pull-out resistance. The mount can slide along the cable tie to adjust orientation as needed. The mount is sold as an assembly with the cable tie.

Material	Polyamide 6.6 recycled, high impact modified, heat stabilized (PA66HIRHS(REC))
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	4000
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.05 "
Height (metric)	1.3 mm
Length (imperial)	6.6 "
Length (metric)	167.9 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.25 " (HEXAGONAL), 0.26 "
Mounting Hole Diameter (metric)	6.35 mm (hexagonal), 6.5 mm
Panel Thickness (imperial)	0.02 - 0.32 "
Panel Thickness (metric)	0.6 - 8.25 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.3 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

