

# TECHNICAL DATA SHEET

**Part No.** 2.5P9C  
**Article No.** 161-05028  
**Type** 2.5P



HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize. Polytetrafluoroethylene-Teflon (PTFE) offers the widest operating temperature range of any material. It's chemically inert and nonflammable. Natural color is milky white. Available by special order in black and colors.

<b>Material</b>	Polytetrafluoroethylene (PTFE)
<b>Operating Temperature</b>	-449°F to +500°F (-267°C to +260°C)
<b>Flammability</b>	UL 94 V-0
<b>Halogen Free</b>	No
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Natural (NA)
<b>Pkg. Qty.</b>	100 ft
<b>Carton Qty.</b>	1200
<b>Customs Number</b>	3926909988

<b>Diameter (imperial)</b>	0.375 "
<b>Diameter (metric)</b>	9.53 mm
<b>Length (imperial)</b>	100.0 ft
<b>Length (metric)</b>	30.48 m
<b>Max. Bundle Diameter (imperial)</b>	2.5 "
<b>Max. Bundle Diameter (metric)</b>	63.5 mm
<b>Min. Bundle Diameter (imperial)</b>	0.31 "
<b>Min. Bundle Diameter (metric)</b>	7.92 mm
<b>Nominal Diameter (imperial)</b>	0.38 "
<b>Nominal Diameter (metric)</b>	9.53 mm
<b>Pitch (imperial)</b>	0.438 "
<b>Pitch (metric)</b>	11.13 mm
<b>Reel Length (imperial)</b>	100.0 ft
<b>Reel Length (metric)</b>	30.48 m
<b>Wall Thickness (imperial)</b>	.030 "
<b>Wall Thickness (metric)</b>	0.76 mm

