

TECHNICAL DATA SHEET

Part No. 2N0C
Article No. 161-05032
Type 2N



HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Material	Polyamide 6 (PA6)
Operating Temperature	-40°F to +250°F (-40°C to +121°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	4000
Customs Number	3926909988

Diameter (imperial)	0.25 "
Diameter (metric)	6.35 mm
Length (imperial)	100.0 ft
Length (metric)	30.48 m
Max. Bundle Diameter (imperial)	2 "
Max. Bundle Diameter (metric)	50.8 mm
Min. Bundle Diameter (imperial)	0.19 "
Min. Bundle Diameter (metric)	4.75 mm
Nominal Diameter (imperial)	0.25 "
Nominal Diameter (metric)	6.35 mm
Pitch (imperial)	0.375 "
Pitch (metric)	9.53 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.48 m
Wall Thickness (imperial)	0.025 "
Wall Thickness (metric)	0.64 mm

