

TECHNICAL DATA SHEET

Part No. 5NFP0C
Article No. 161-05079
Type 5NFP



HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Material	Polyethylene (PE)
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
Halogen Free	No
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	300
Customs Number	3926909988

Diameter (imperial)	1.0 "
Diameter (metric)	25.4 mm
Length (imperial)	100.0 ft
Length (metric)	30.48 m
Max. Bundle Diameter (imperial)	7.01 "
Max. Bundle Diameter (metric)	178.0 mm
Min. Bundle Diameter (imperial)	1 "
Min. Bundle Diameter (metric)	25.4 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	25.4 mm
Pitch (imperial)	1.0 "
Pitch (metric)	25.4 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.48 m
Wall Thickness (imperial)	0.095 "
Wall Thickness (metric)	2.41 mm

RoHS✓

