

TECHNICAL DATA SHEET

Part No. 3N9C
Article No. 161-05051
Type 3N



HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Material	Polyamide 6 (PA6)
Operating Temperature	-40°F to +250°F (-40°C to +121°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	100 ft
Carton Qty.	1200
Customs Number	3926909988

Diameter (imperial)	0.5 "
Diameter (metric)	12.7 mm
Length (imperial)	100.0 ft
Length (metric)	30.48 m
Max. Bundle Diameter (imperial)	4.02 "
Max. Bundle Diameter (metric)	102.0 mm
Min. Bundle Diameter (imperial)	0.37 "
Min. Bundle Diameter (metric)	9.52 mm
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	12.7 mm
Pitch (imperial)	0.5 "
Pitch (metric)	12.7 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.48 m
Wall Thickness (imperial)	0.035 "
Wall Thickness (metric)	0.89 mm

