

TECHNICAL DATA SHEET

Part No. 161-46100
Article No. 161-46100
Type SBPEMC4



SBPEMC provides flexible, durable cable and hose protection. It is ideal for food-processing machines and related environments. Protects against abrasion, making it appropriate for applications where movement is an issue.

Material	Polyethylene (PE), Stainless Steel (SS)
Operating Temperature	-76°F to +176°F (-60°C to +80°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Blue (BU)
Pkg. Qty.	98.43 ft
Carton Qty.	1
Customs Number	3926909988

Diameter (metric)	4 mm
Max. Bundle Diameter (imperial)	0.79 "
Max. Bundle Diameter (metric)	20 mm
Min. Bundle Diameter (imperial)	0.2 "
Min. Bundle Diameter (metric)	5 mm
Nominal Diameter (imperial)	0.19 "
Nominal Diameter (metric)	4 mm
Pitch (metric)	7.8 mm
Reel Length (metric)	30 m
Wall Thickness (imperial)	0.039 "
Wall Thickness (metric)	1.0 mm

