

TECHNICAL DATA SHEET

Part No. 169-60311
Article No. 169-60311
Type CTPFR1120



HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The Polyethylene flame retardant material provides additional protection that is suitable for applications requiring a self-extinguishing material and complies with UL 94 V2 standards.

Material	Polyethylene, flame retardant (PE-FR)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	150.0 ft
Carton Qty.	150
Customs Number	3926909988

Inner Diameter (imperial)	1.647 "
Inner Diameter 2 (metric)	41.83 mm
Length (imperial)	150.0 ft
Length (metric)	45.7 m
Nominal Diameter (imperial)	1.5 "
Nominal Diameter (metric)	38.1 mm
Outside Diameter (imperial)	1.947 "
Outside Diameter (metric)	49.45 mm
Wall Thickness (imperial)	0.006 "
Wall Thickness (metric)	0.152 mm

