

TECHNICAL DATA SHEET

Part No. 170-03027
Article No. 170-03027
Type BSPA66120



A pliable yet durable nylon sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion. Used on hoses, pipes, wiring harnesses and cables installed in cars, trucks, military vehicles, trains and industrial equipment. Protects delicate wiring in engine compartments and near exhaust systems or used to organize wires and breakouts in electrical harnesses.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-49°F to +302°F (-45°C to +150°C)
Melting Point	+491 °F (+255 °C)
Abrasion Resistance	High
Flammability	UL 94 V-2, FMVSS 302
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	10
Customs Number	5808100000

Description	Standard-Size Reels
Max. Bundle Diameter (imperial)	0.75 "
Max. Bundle Diameter (metric)	19.1 mm
Min. Bundle Diameter (imperial)	0.37 "
Min. Bundle Diameter (metric)	9.5 mm
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	12.7 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.4 m

