

TECHNICAL DATA SHEET

Part No. 170-03061
Article No. 170-03061
Type BSHTFG100



An extremely high-temperature resistant sleeving designed to protect wires and cables subjected to continuous temperature variations, vibration, abrasion, and mechanical stress. Perfect for engine manifolds and exhaust systems or any application where fire and exceeding temperatures create a hazard to workforce and equipment.

Material	Glass Fiber (GF)
Operating Temperature	-94°F to +1202°F (-70°C to +650°C)
Melting Point	+2048 °F (1120 °C)
Abrasion Resistance	Very high
Flammability	UL VW-1
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	25 ft
Carton Qty.	1
Customs Number	7019905150

Description	Standard-Size Reels
Max. Bundle Diameter (imperial)	1.63 "
Max. Bundle Diameter (metric)	41.3 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	25.4 mm
Reel Length (imperial)	25.0 ft
Reel Length (metric)	7.6 m
Wall Thickness (imperial)	0.057 "
Wall Thickness (metric)	1.45 mm

