

# TECHNICAL DATA SHEET

**Part No.** 170-03124  
**Article No.** 170-03124  
**Type** BSPSW180B



A lateral split semi-rigid braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.

<b>Material</b>	Polyester (PET)
<b>Operating Temperature</b>	-94°F to +257°F (-70°C to +125°C)
<b>Melting Point</b>	+482 °F (+250 °C)
<b>Abrasion Resistance</b>	Medium
<b>Flammability</b>	UL 94 V-0
<b>Halogen Free</b>	Yes
<b>UV Resistant</b>	Yes
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	400 ft
<b>Carton Qty.</b>	1
<b>Customs Number</b>	5808100000

<b>Description</b>	Bulk-Size Reel
<b>Max. Bundle Diameter (imperial)</b>	0.13 "
<b>Max. Bundle Diameter (metric)</b>	3.2 mm
<b>Min. Bundle Diameter (imperial)</b>	0.1 "
<b>Min. Bundle Diameter (metric)</b>	2.54 mm
<b>Nominal Diameter (imperial)</b>	0.125 "
<b>Nominal Diameter (metric)</b>	3.18 mm
<b>Reel Length (imperial)</b>	400.0 ft
<b>Reel Length (metric)</b>	121.9 m
<b>Wall Thickness (imperial)</b>	0.024 "
<b>Wall Thickness (metric)</b>	0.61 mm

