

TECHNICAL DATA SHEET

Part No. 170-03151
Article No. 170-03151
Type BSHKLP200B



Designed for the quick and easy management of wires, this expandable sleeving has an internal hook and loop strap that is able to adhere to its outer PET braid, delivering flexibility that allows it to fit around odd-shaped connectors. Its color-matched hook and loop closure provides for an easy on and off installation, as well as instant and convenient access for harness break-outs and networks. The primary application for this sleeving is the wrapping and bunching of cables in a deployed situation or when frequent access to cables is necessary.

Material	Polyester (PET)
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL 94 V-0, FAR 25
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	1
Customs Number	5808100000

Max. Bundle Diameter (imperial)	2 "
Max. Bundle Diameter (metric)	50.8 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	2 "
Nominal Diameter (metric)	50.8 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.5 m
Wall Thickness (imperial)	0.025 "
Wall Thickness (metric)	0.635 mm

